

# **Bucher XPro**

The Bucher XPro pneumatic press includes the essential elements of Bucher presses. A small-capacity press, it is ideal for pressing fresh grapes, fermented pomace or selecting quality batches. Highly manoeuvrable, space-saving and easy to use, the Bucher XPro press fits easily into any cellar.















# **Technical description**

Configurations		XPro	5 XPro 8	XPro 15
For filling via door.		1 porte manuell	e 1 porte manuelle	1 manual door
Axial filling			x	x
Automatic programming			x x	х
Prim' Step programming			x	x
Number of perforated spouts			3	3
Spout surface area (% of 1/2-tank surface area)		4	41	30
Electropolished and extractable chutes			x x	x
Juice trough on wheels			x	x
Pomace emptying through doors			x	х
Technical data	XPro 5	XPro 8		XPro 15
Capacity of juice trough	260	370		450
Unladen weight (kg)	420	520		650
Power (kW)	1.5	2.75		OR
Supply voltage:	230	230		420 - 50Hz or 460 - 60Hz

# **Bucher XPro**

Length (mm)	1900	2550	2780
Width (mm)	1000	1000	1250
Height (mm)	1320	1320	1440
Height under beam (mm)	400	400	410

#### The benefits

## Adaptability

The Bucher XPro pneumatic press has a sliding door. Its large opening makes it easy to fill the press and also makes it easy to empty the pomace and to clean it.

Bucher Xpro has removable, perforated spouts, which makes it quick and easy to wash the press

The maceration function is included through the shutters at the end of the spouts.

The PLC has 6 modifiable, automatic programmes and two Prim'Step sequential programmes for the duration of the stages and the number of rotations at the end of the cycle.

The must is recovered easily with the juice trough on wheels under the press.

## **Options**

#### **Axial filling**

Only for Bucher XPro 15 presses

#### Maintenance

The closed tank with perforated, self-cleaning gutters (Bucher patent) ensures the evacuation of musts during pressing and generates very low levels of sludge.

Easy to clean, thanks to Bucher Vaslin's patented perforated spout extraction system.

Electro-polishing of perforated trunking

## **Bucher Vaslin North America**

3100 Dutton Avenue Suite 134D Santa Rosa, CA 95407 (707) 823-2883

